

TSU-C/D 290-340-400-450

Ice thermal storage

Engineering data

REMARK: Do not use for construction. Refer to factory certified dimensions & weights. This page includes data current at time of publication, which should be reconfirmed at the time of purchase. In the interest of product improvement, specifications, weights and dimensions are subject to change without notice.

General notes

- 1. All dimensions are in mm. Weights are in kg.
- 2. Unit should be continuously supported on a flat level surface.
- 3. H_1 = installed height. Coils connections are closed and filled with inert gast for shipping and storage. Add 130 mm for shipping height.
- 4. Refrigerant charge listed is operating charge for pump recirculated bottom feed. For other feed systems, consult your BAC representative.

Last update: 01/01/2025

TSU-C/D 290-340-400-450



1. Coil connections; 2. Make up ND50; 3. Overflow ND50; 4. Water out; 5. Water in; 6. Drain ND50; 7. ICE LOGIC®.



Model	Approx. Ship. Weight (kg)	Approx. Oper. Weight (kg)	Air Pump (kW)	Water Volume (I)	Pull Down Volume (I)	Coil Volume (L)	R717 charge (kg)	Water Conn. In ND (mm)	Water Conn. Out ND (mm)	н	H1	L	W
TSU-	5600	2521	1,75	1870	492	878	379	150+	150	2160	2360	3683	2982
290C		0		0				2x80					
TSU-	6245	2926	1,75	2196	606	1020	440	150+	150	2160	2360	4293	2982
340C		0		0				2x80					
TSU-	7210	3363	1,75	2512	681	1161	501	150+	150	2160	2360	4877	2982
400C		0		0				2x80					
TSU-	7900	3768	1,75	2847	757	1275	550	150+	150	2160	2360	5486	2982
450C		0		0				2x80					